Ianufacturer: SWECO Inc. quipment: Vibro Energy Separator 48 inch				
Sr. No.	Description	Part No.	Qty Required	
	Snap-in spring spool	S48K00226	36	
1	Spring Spring spool	\$48\$00201	24	
2	Center Tie Down Assy	S48S00942	10	
3	Balance spring Assembly	S48C01910	2	
4		S48S00525	10	
5	Oval Inspection Cover Assembly	548581100	12 .	
6	"V" Clamp ring Assembly including channel gasket	S48C00707	10	
7 8	Top Weight Plates Ball Tray Assembly SS with screen 8 mesh and silicone balls	S48C81599	2	
		S48K11114	1000	
9	Nylon sliders Ball Tray Balls (Silicone)	S48K01606	100	
	Metal Cover Assy w/ 1 Inspection Opening	\$48\$81300	2 .	
11		S48N01912	2 :	
12	Center Cap	S48S01044	10	
13	Self-Cleaning Screen Kit 48" Supertaut Plus Screen with 18MG mesh 316SS, with center hole (WCH), complete with gasket	48A8A018M	3	
15	48" Supertaut Plus Screen with 20MG mesh 316SS, with center	48A8A020M	3	
-	48" Supertaut Plus Screen with 24MG mesh 316SS, with center	48A8A024M	. 3	

		S48K00226	36
-	Snap-in spring spool	\$48\$00201	24
2	Spring	548500942	10
3	Center Tie Down Assy	S48C01910	2
4	Balance spring Assembly	\$48\$00525	10
5	Oval Inspection Cover Assembly		12 .
6	"V" Clamp ring Assembly including channel gasket	S48S81100	
7	Top Weight Plates	S48C00707	10
8	Ball Tray Assembly SS with screen 8 mesh and silicone balls	S48C81599	2
9	Nylon sliders	S48K11114	1000
10	Ball Tray Balls (Silicone)	S48K01606	100
	Metal Cover Assy w/ 1 Inspection Opening	\$48\$81300	2 .
11		S48N01912	2
12	Center Cap Self-Cleaning Screen Kit	S48S01044	10
13	48" Supertaut Plus Screen with 18MG mesh 316SS, with center hole (WCH), complete with gasket	48A8A018M	3
15	48" Supertaut Plus Screen with 20MG mesh 316SS, with center hole (WCH), complete with gasket	48A8A020M	3
16	48" Supertaut Plus Screen with 24MG mesh 316SS, with center hole (WCH), complete with gasket	48A8A024M	3
17	48" Supertaut Plus Screen with 35MG mesh 316SS, with center hole (WCH), complete with gasket	48A8A030M	3
18	48" Supertaut Plus Screen with 45MG mesh 316SS, with center hole (WCH), complete with gasket	48A8A045M	. 3
19	48" Supertaut Plus Screen with 400MG mesh 316SS, with center	48A8A400M	2
20	48" Supertaut Plus Screen with 30MG mesh 316SS, with center	48A8A500M	2